

GESIPA® assembly cell

NEW

GESIPA® assembly cell

The new GESIPA® assembly cell guarantees optimum, precise handling with a wide range of GESIPA® processing devices and a workspace tailored perfectly to the customer's requirements.

The desk is adapted individually to customer requirements and designed ergonomically (e.g. adjustable height). Everything – be it the desk, work piece socket, compressed air supply, electrical supply or processing tools – comes from one source, with process monitoring on request.

The optimised work piece socket allows the desk to be converted for different products and processing tools easily, saving costs.


The GESIPA® assembly cell is produced from high quality materials and components. Needless to say, you also have the option of transferring system components already used at your company.

Advantages

- Ergonomic working
- Individually adjustable
- Existing work tools can be integrated
- Easy and time-saving conversion for other products from your portfolio

More information on the individually adjusted assembly cell on request.
Contact: Uwe Herth,
Head of BU Equipment Manufacturer,
uwe.herth@gesipa.com

The GESIPA® assembly cell – ergonomic and individually adjustable



Operating status display

The signal light installed on the desk uses different colours to show the process status.




Counting device

The counting device registers and counts the torn off residual rivet mandrels.



GESIPA® setting tool

The setting tool is completely integrated in the assembly cell.



Individual work piece carrier

The optimised work piece carrier allows the desk to be converted for different products and processing tools easily, saving costs.



Foot pedal

The foot pedal allows you to use both hands to join individual parts and fasten the components to be riveted in place.



Example:
Can be individually adjusted for each customer